



MANUAL TRAY SEALER

B 185

These manual tray machine are perfect for sealing a fitting hermetic film on **small and medium-sized trays**. They are equipped with a soft keyboard for temperature control and mechanical locking on the MV model.

Maximum tray size: 235 x 185 mm



B 185



B 185 MV

Uses



Catering professions



Groceries & supermarkets



Optional: made-to-measure mould to fit to your trays formats.



- ✓ Practical and easy to use for sealing small and medium-sized trays up to a maximum size of 235 x 185 mm.
- ✓ Manual closure by double handles or by mechanical locking (MV) for easy and regular sealing.
- ✓ Compact and space-saving: ideal for countertop use.
- ✓ Stainless steel structure for easy cleaning and better resistance to disinfectants (reduces retention zones).



1 year warranty⁽¹⁾

⁽¹⁾Except wear parts










Compatible materials
Bio-sourced or compostable



Compliance with
CE standards

FOOD range

TECHNICAL DATA

MODELS							
B 185	50 x 25,2 x 52,5 cm	185 mm (max)	190 mm (max)	soft keyboard	10 kg	600 W	230 V 50/60 Hz
B 185 MV	56,5 x 25,2 x 55,5 cm	185 mm (max)	190 mm (max)	soft keyboard	11 kg	600 W	230 V 50/60 Hz

* Dimensions open cover

EQUIPMENT


MV system =
mechanical locking
for easy tightening



ADAPTED TOOLS

MOULD

Options: made-to-measure mould for other tray dimension
(please contact us).



TRAY

Max. tray height




OPERATING PRINCIPLE




Place your tray and its contents on the mould.




Unroll the film over the tray.



Lower the handle to cut and seal the film.



Keep the 2 handles pressed together for a few seconds.



The tray is sealed and ready to use.

Need more information?



Contact the sales department: +33 (0)4 74 00 59 54